

# Light-Source Mainframe

## Specification & User Manual

## Table of Contents

<b>Disclaimer .....</b>	<b>3</b>
<b>Range Of Limitations.....</b>	<b>3</b>
<b>Dimensions and Materials .....</b>	<b>3</b>
<b>Features .....</b>	<b>3</b>
<b>Specifications .....</b>	<b>4</b>
<b>Applications .....</b>	<b>4</b>
<b>Guide .....</b>	<b>5</b>
<b>Operating Instructions .....</b>	<b>5</b>
<b>Maintenance.....</b>	<b>6</b>
<b>Inspection Datasheet.....</b>	<b>6</b>
<b>Shipping Information.....</b>	<b>6</b>
<b>Product Guarantee.....</b>	<b>6</b>
<b>Warranty.....</b>	<b>6</b>
<b>Ordering Information.....</b>	<b>6</b>
<b>Contact Information.....</b>	<b>7</b>

## Disclaimer

The information noted within this document is purely for informational purposes only. Please note that SENKO Advanced Components, Inc. does not warrant or assume any legal liability or responsibility for the accuracy, completeness or usefulness of any information or processes disclosed. Specifications are subject to change without notice.

The following information is strictly confidential. Reproduction or disclosure to any third party is not permitted without the express written consent of SENKO Advanced Components, Inc. The SENKO Group logo as well as the name "SENKO" are Registered Trade Marks ® of SENKO Advanced Components, Inc. All other Trade Marks referred to are the property of the respective rights holders.

For further information or general comments, please contact one of our sales offices.

## Range Of Limitations

The Product Information found herein pertain to the Light Source Mainframe, Part Number

## Dimensions and Materials

All the materials comply with RoHS Restricted Hazardous Substances as detailed in “**DIRECTIVE 2002/95/EC OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 27 January 2003 on the Restriction of the use of Certain Hazardous Substances in Electrical and Electronic Equipment (RoHS)**”

## Features

- Compact, portable, light and rugged design.
- No warm up time.
- Interchangeable SFP Module design.
- High wavelength flexibility with interchangeable SFP Modules.
- High Output Power stability.
- Stable output wavelength.
- Excellent re-connection repeatability.
- Low Voltage Battery warning.
- Compatible with LC Connectors.
- Easy to use.
- Operates in CW (Continuous Wave) or Pulse Mode 270 Hz / 2 KHz.
- Dust-proof design keeps fiber connectors clean.
- LED indicator for Power and Low Battery indicators.


## Specifications

<b>Laser Class</b>	<b>Class 1</b>
<b>Wavelength (nm)</b>	<b>850, 1300, 1310, 1550 1270, 1290, 1310, 1330, 1350, 1370, 1390, 1410, 1430, 1450, 1470, 1490, 1510, 1530, 1550, 1570, 1590, 1610, 1625</b>
<b>Output Power</b>	<b>&gt; 0.5 mW @ 25°C into 9 μm fiber</b>
<b>Mode</b>	<b>CW / Pulse Mode 270 Hz / 2 KHz</b>
<b>Battery Type</b>	<b>AAA 1.5 V x 2</b>
<b>LED Indicator</b>	<b>Power On ( GREEN ) / Battery Low ( RED)</b>
<b>Output Power Accuracy</b>	<b>+/- 0.2 dB</b>
<b>Output Power Stability ( 1 HR )</b>	<b>+/- 0.05 dB</b>
<b>Operating Temp.</b>	<b>0°C ~ 50°C</b>
<b>Storage Temp.</b>	<b>0°C ~ 70°C</b>

## Applications

- Maintenance CATV / Telecom / FTTH in Singlemode or Multimode optical fiber network.
- Standard laboratories.
- High throughput quality assurance.
- Onsite installation/maintenance.

## Guide



1. Dust Cap
2. SFP Module: Interchangeable single LC connector SFP Module.
3. LED Display
4. On/Off Button
5. Mode Switch: to select Continuous Wave or Pulse Modes at 270Hz or 2KHz.

## Operating Instructions

1. Remove the Dust Cap and insert the desired SFP Module.
2. **INITIAL CALIBRATION**: With the desired SFP Module loaded, close the Dust Cap then turn on the Light Source by pressing the On/Off Button. Once the unit is calibrated the LED will turn green.
3. Turn the Light Source off by pressing the On/Off button.
  - 3i. Remove the Dust Cap.
  - 3ii. Insert one end of the jumper to be tested directly into the output port of the Light Source.
  - 3iii. Insert the other end of the jumper into the Fiber Meter.
  - 3iv. If a test jumper has to be used, then insert the other end into the Fiber Meter to obtain the loss of the test jumper as reference. Remove the test jumper from the Fiber Meter, insert it into the appropriate adapter and then insert either end of the jumper to be tested to the adapter and Fiber Meter.
4. Slide the Mode Switch to select CW Mode or Pulse Mode 270 Hz / 2 KHz.
5. Turn the unit on by pressing the On/Off button.

### Important Notes:

- **DO NOT** look into the output port of the Light Source when it is on. Doing so may damage your eyes.
- Do not touch the SFP Module's electrical connector.
- Do not touch the ferrule to avoid contaminating the connector.
- Keep the fiber connector dust cap on at all times when the device is not in use.
- Use suitable cleaning tools to clean the fiber before testing to obtain the desired test results and extend the service life of the device.
- When the LED shows "CB" (Check Battery), this means that the batteries are almost drained and in low voltage status. Immediate replacement of the batteries is recommended.

## Maintenance

This tool requires no maintenance in stead of periodic battery charges. Like any other electronic equipment, this tool should be kept away from water, high damp, dust, electricity, and environments of extreme temperature. Do not drop this tool on hard surface. Modifying internally any of this tool components can cause a malfunction and will invalidate the manufacturer's warranty.

## Inspection Datasheet

Certificate of Compliance is included with each shipment.

## Shipping Information

All items are packed in a secure fashion so as to prevent any damage during transit.

## Product Guarantee

The buyer of this product should inspect the goods upon arrival, and within five (5) business days should notify SENKO of any conditions which may prevent the acceptance of this product. In the event of a claim, appropriate measures will be taken to investigate the cause. Claims must be made in accordance to the conditions stated in the Standard Terms and Conditions of Sale.

## Warranty

The manufacturer warrants this product to be free of defects in workmanship and materials for a period of 1 year after purchase. This warranty (excluding batteries) is solely limited to the repair and replacement of original parts, which are defective in workmanship of materials. All other costs should be the sole responsibility of the owner. This warranty does not cover any defects, damage, and deterioration due to misuse, alteration, or negligence.

## Ordering Information

Part Number	Light Source SFP Plug-In Module	Wavelength (nm)
AFT-G-MF-LS	Light Source Mainframe	-
AFT-G-LS-M-850	VCSEL - Light Source SFP Plug-In Module	850 nm
AFT-G-LS-M-1300	LED - Light Source SFP Plug-In Module	1300 nm
AFT-G-LS-S-1310	FP LD - Light Source SFP Plug-In Module	1310 nm
AFT-G-LS-S-1550	FP LD - Light Source SFP Plug-In Module	1550 nm
AFT-G-LS-1270-1625	CWDM DFB LD - Light Source SFP Plug-In Module	1270 nm ~ 1625 nm

## Contact Information

### Europe

Italy: +39-011-839-9828  
Email: [Sale-Europe@senko.com](mailto:Sale-Europe@senko.com)

Poland: +48 (71) 7988152  
Email: [Sales-Poland@senko.com](mailto:Sales-Poland@senko.com)  
UK: +44 (0) 1189-821600  
Email: [Sale-Europe@senko.com](mailto:Sale-Europe@senko.com)

### Asia

Hong Kong: +852-2121-0516  
Email: [Sales-Asia@senko.com](mailto:Sales-Asia@senko.com)

Japan: +81 (0) 3-5825-0911  
Email: [Sales-Asia@senko.com](mailto:Sales-Asia@senko.com)

Shanghai: +86-21-6418-1134  
Email: [Sales-Asia@senko.com](mailto:Sales-Asia@senko.com)

Shenzhen: +86-21-5830-4513  
Email: [Sales-Asia@senko.com](mailto:Sales-Asia@senko.com)

### Americas

USA East: +1-508-481-9999  
Email: [Sales-America@senko.com](mailto:Sales-America@senko.com)

USA West: +1-858-623-3300  
Email: [Sales-America@senko.com](mailto:Sales-America@senko.com)

### Asia Pacific

Australia: +61 (0) 3-9755-7922  
Email: [Sales-Asia-Pacific@senko.com](mailto:Sales-Asia-Pacific@senko.com)

### Middle East

Dubai: +971 4-8865160